




TS970, TS971 Control board connection to 2 pcs ELS 500 mini photo cells

TS970, TS971 Control board



1. 2.1-2.2 original resistor
2. 2.3-2.4 additional resistor 8K2
3. To activate impulse operation UP-DOWN Program 1 set to 3
4. If Photo cells installed in door way learn photo cell crossing point at control. Activate program 3.2 operate 2 full cycles



Conection only for RDS 3000 rolling high speed doors



Riga Door Systems
we open the world

Malas, Vetras, Marupe LV-2167, Riga district, Latvia; web: www.rigadoors.lv

Designed by

Sheet Format

Date

A3 2026-01-29

TS970-971+ 2PCS ELS500 MINI PHOTO

TS970-971+ 2PCS ELS500 MINI PHOTO

Rev.

00

Sheet

1 / 1